


## **MPXV1D1740LR68**

Aliases (UPI2X11740VR68) KEMET, MPXV, Metal Composite, 20%, 680 nH





General Information	
Series	MPXV
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	40 (K) Temperature Rise Max.

## Click here for the 3D model.

Dimensions	
L	17mm +/-0.5mm
W	17.1mm +/-0.5mm
Т	4mm MAX
G	11.9mm NOM

Packaging Specifications		
Typical Component Weight	6.3 g	
Packaging	T&R, 330mm	
Packaging Quantity	100	

Specifications	
Inductance	0.68 uH (100 kHz)
Inductance Tolerance	20%
Rated Current	32 A (Irms, 40C Rise By Self Heating)
Saturation Current	37 A (Isat, 20% Drop In Inductance), 55 A (Isat, 30% Drop In Inductance)
Temperature Range	-55/+155°C
Shielded	Yes
DC Resistance	2 mOhms
DC Resistance	2 mOhms
Self-Resonant Frequency	38 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/12/2025 © 2006 - 2025 YAGEO