



Click [here](#) for the 3D model.

General Information

Style	Bolt-On
Description	Langevin Bolt-On Transducers
RoHS	With Exemptions
SCIP Number	6629125f-50d3-4e75-ae76-25e0bc1955b0
Notes	Straight construction.
REACH	SVHC (PZT - CAS 12626-81-2)

Dimensions

D	15mm NOM
L	40.8mm NOM

Packaging Specifications

Typical Component Weight	30
Packaging	Bulk Tray, Box
Packaging Quantity	160

Specifications

Series	NBL
Capacitance	850 pF
Resonant Frequency	60 kHz
Dynamic Admittance	25 mS
Mechanical Q	500 Qm
Allowable Velocity	50 cm/S
Allowable Power	2.5
Temperature Range	-40/+120°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.