


PME271YB5220MR19T0

Aliases (P272QM223M300L) PME271Y/P272, Film, Metallized Paper, Safety, 0.022 uF, 20%, 1,000 VDC, 300 VAC (Y2), 115°C, 15.2 mm



Click	here	for t	he 3	D m	odel

General Information	
Series	PME271Y/P272
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	Y2
Qualifications	ENEC, UL, cUL, CQC
AEC-Q200	No
Construction	Molded
Typical Component Weight	2.7 g
Miscellaneous	SRF= 9.8 MHz.

Dimensions	
L	18.5mm MAX
Н	13mm MAX
Т	7.3mm MAX
S	15.2mm +/-0.4mm
НО	18.5mm +/-0.5mm
F	0.8mm +/-0.05mm

Packaging Specifications		
Packaging	T&R	
Packaging Quantity	400	

Specifications	
Capacitance	0.022 uF
Tolerance	20%
Voltage DC	1000 VDC
Voltage AC	300 VAC (Y2)
Temperature Range	-40/+115°C
Rated Temperature	115°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	1,400 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/24/2025 © 2006 - 2025 YAGEO