


PEH226MG3370QE1

Not for New Design

PEH226, Aluminum, Aluminum Electrolytic, 370 uF, -10/+30%, 63 VDC, -40/+150°C

YAGEO:



Note: '()' correspond to the letters used in the product bulletin

Click here for the 3D model.

Dimensions	
D	16mm +/-0.5mm
L	35.7mm +/-1mm
LL	3.3mm +/-0.5mm
F	1mm +/-0.3mm

Packaging Specifications	
Packaging	Tray

General Information	
Series	PEH226
Dielectric	Aluminum Electrolytic
Style	Radial Crown
Description	Radial Crown Aluminum Electrolytic
RoHS	Yes
Lead	Radial Crown
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Typical Component Weight	11 g
Shelf Life	520 Weeks

Specifications	
Capacitance	370 uF
Tolerance	-10/+30%
Voltage DC	63 VDC
Temperature Range	-40/+150°C
Rated Temperature	150°C
Life	6300 Hrs (Rated Voltage At 125C), 1500 Hrs (Rated Voltage At 150C)
ESR	155 mOhms (100Hz 20C), 37 mOhms (100kHz 20C), 19.2 mOhms (5-100kHz 150C)
Ripple Current	13.6 Amps (5kHz 125C, With Heat Sink), 8.6 Amps (5kHz 140C, With Heat Sink), 3.9 Amps (5kHz 150C, With Heat Sink), 5.1 Amps (5kHz 125C), 6.4 Amps (>=5kHz 125C Max)
Leakage Current	70 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/16/2025 © 2006 - 2025 YAGEO