



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--|
| Series | PEG124_125C |
| Dielectric | Aluminum Electrolytic |
| Style | Axial |
| Description | Long Life Axial Aluminum Electrolytic |
| Features | Long Life |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Halogen Free | Yes |
| Typical Component Weight | 4 g |
| Miscellaneous | Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information. |
| Notes | L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article. |

Dimensions

| | |
|----|-----------------|
| D | 10mm +/-0.5mm |
| L | 29mm +/-1mm |
| L1 | 35mm MIN |
| LL | 42mm +3/-2mm |
| F | 0.8mm +/-0.03mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 200 |

Specifications

| | |
|-------------------|---|
| Capacitance | 150 uF |
| Tolerance | -10/+30% |
| Voltage DC | 16 VDC |
| Temperature Range | -40/+125°C |
| Rated Temperature | 125°C |
| Life | 2000 Hrs |
| ESR | 1100 mOhms (100Hz 20C), 710 mOhms (100kHz 20C) |
| Ripple Current | 0.287 Amps (100Hz 125C), 1.5 Amps (5kHz 60C), 0.61 Amps (5kHz 125C) |
| Leakage Current | 7 uA (5min 20°C) |
| Inductance | 6 nH (ESL) |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.