




PEH532, Aluminum, Aluminum Electrolytic, 220 uF, 20%, 350 VDC, -40/ +105°C, 10 mm



General Information	
Series	PEH532
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No
Typical Component Weight	24 g
Notes	Add 0.5mm To D And 1mm To L For Sleeving.
Shelf Life	208 Weeks

Click here for the 3D model.

Dimensions	
D	25mm +/-0.5mm
L	35mm +/-1mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm
Packaging Specifications	
Packaging	Tray

100

Packaging Quantity

Specifications	
Capacitance	220 uF
Tolerance	20%
Voltage DC	350 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	1500 Hrs (Rated Voltage And Ripple Current At 105C), 2000 Hrs (Rated Voltage At 105C)
ESR	600 mOhms (100Hz 20C), 380 mOhms (100kHz 20C)
Ripple Current	0.87 Amps (100Hz 105C), 2.4 Amps (20kHz 40C)
Leakage Current	231 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute.	te - and
we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who leads to the contract of the customer application or use.	nave the
requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provide	ed by us
with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.	•

Generated 11/05/2025 © 2006 - 2025 YAGEO