


PEH169QA368VMU2

Aliases (A371GC681M160A)

PEH169, Aluminum, Aluminum Electrolytic, 680 uF, 20%, 160 VDC, -40/+85°C, 13 mm



Click here for the 3D n	nodel
-------------------------	-------

Dimensions	
D	36.6mm +/-1mm
L	51.5mm +/-1mm
T	4.4mm NOM
S	13mm +/-0.5mm
F	8mm +/-0.5mm
DT	8mm NOM
LT	58.9mm +/-1mm

Packaging Specifications	
Sleeving	Yes
Packaging	Bulk, Bag
Packaging Quantity	42

General Information	
Series	PEH169
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals M5
Mounting	Through-Hole
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	70 g
Notes	Dimensions D And L Include Sleeving. MS (MxH) = M8x12.
Shelf Life	156 Weeks

Specifications	
Capacitance	680 uF
Tolerance	20%
Voltage DC	160 VDC
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	14000 Hrs (Rated Voltage And Ripple Current At 85C)
ESR	190 mOhms (100Hz 20C), 98 mOhms (100kHz 20C)
Ripple Current	3 Amps (100Hz 85C), 14.3 Amps (10kHz 50C), 9.7 Amps (10kHz 40C)
Leakage Current	4326.4 uA (5min 20°C)
Inductance	12 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/01/2025 © 2006 - 2025 YAGEO