



Click [here](#) for the 3D model.

#### General Information

Series	PHH223
Dielectric	Hybrid Polymer
Style	Radial Crown
Description	Hybrid Radial Crown Capacitors
RoHS	Yes
Lead	Radial Crown
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	true
Typical Component Weight	11 g
Shelf Life	520 Weeks

#### Dimensions

D	18.2mm +/-0.5mm
L	27.7mm +/-1mm
LL	3.3mm +/-2mm
F	1mm +/-0.03mm

#### Packaging Specifications

Packaging	Tray
-----------	------

#### Specifications

Capacitance	800 uF
Capacitance Tolerance	20%
Voltage DC	63 VDC
Temperature Range	-40/+125°C
Rated Temperature	125°C
ESR	85 mOhms (100Hz 20C), 4.2 mOhms (100kHz -40C to 125C)
Ripple Current	42.5 Amps (100kHz 90C), 36 Amps (100kHz 105C), 24.4 Amps (100kHz 125C)
Leakage Current	252 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.