



General Information

Series	PEV228
Dielectric	Aluminum Electrolytic
Style	Vertical Crown SMD
Description	Radial Crown Surface Mount Aluminum Electrolytic
RoHS	Yes
Lead	Radial Crown SMD
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Typical Component Weight	13 g
Shelf Life	520 Weeks

Dimensions

L	28.9mm +/-1mm
W	19mm +/-0.5mm
T	2.5mm +/-0.3mm
S	3mm +/-0.3mm
E	24.5mm +/-0.5mm

Packaging Specifications

Packaging	Tray
-----------	------

Specifications

Capacitance	1,700 uF
Capacitance Tolerance	-10/+30%
Voltage DC	40 VDC
Temperature Range	-40/+150°C
Rated Temperature	150°C
Life	8400 Hrs (Rated Voltage At 125C), 2000 Hrs (Rated Voltage At 150C)
ESR	54.5 mOhms (100Hz 20C), 24.2 mOhms (100kHz 20C), 11 mOhms (5-100kHz 150C)
Ripple Current	18.8 Amps Maximum with heat-sink (5kHz 125C)
Leakage Current	208 uA (5min 20°C)