


R46KF2470DQH1K

Aliases (46KF2470DQH1K) R46 275 VAC 125C, Film, Metallized Polypropylene, Safety, 0.047 uF, 10%, 560 VDC, 275 VAC (X2), 125°C, 10 mm



General Information	
Series	R46 275 VAC 125C
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Safety Class	X2
Qualifications	ENEC, UL, cUL, CQC
AEC-Q200	No

Click here for the 3D model.

Dimensions	
L 1	13mm +0.2/-0.5mm
Н 1	12mm +0.1/-0.5mm
Т	6mm +0.2/-0.5mm
S 1	10mm +/-0.4mm
HO 1	18.5mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications	
Packaging	Ammo, 360x340x59mm, Box
Packaging Quantity	680

Specifications	
Capacitance	0.047 uF
Tolerance	10%
Voltage DC	560 VDC
Voltage AC	275 VAC (X2)
Temperature Range	-40/+125°C
Rated Temperature	125°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	100 GOhms
Max dV/dt	500 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/30/2025 © 2006 - 2025 YAGEO