

R49AR41500001K

Aliases (49AR41500001K)

R49 310 VAC, Film, Metallized Polypropylene, Safety, 1.5 uF, 10%, 800 VDC, 310 VAC (X1), 110°C, 27.5 mm



Click [here](#) for the 3D model.

General Information

Series	R49 310 VAC
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut
Safety Class	X1
Qualifications	ENEC, UL, cUL
AEC-Q200	No
Typical Component Weight	21.92 g

Specifications

Capacitance	1.5 uF
Tolerance	10%
Voltage DC	800 VDC
Voltage AC	310 VAC (X1)
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	20 GOhms
Max dV/dt	200 V/us

Dimensions

L	32mm +0.3/-0.7mm
H	33mm +0.1/-0.7mm
T	18mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	256

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.