

R71VN4150AA30M

Aliases (71VN4150AA30M)

R71, Film, Metallized Polypropylene, General Purpose, 1.5 uF, 20%, 520 VDC, 105°C, 22.5 mm



Click [here](#) for the 3D model.

General Information

Series	R71
Dielectric	Metallized Polypropylene
Style	Radial
Features	PFC and Pulse
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut
AEC-Q200	No
Typical Component Weight	7.168 g
Miscellaneous	Above 105C DC And AC Voltage Derating Is 4%/C.

Dimensions

L	26.5mm +0.3/-0.5mm
H	20mm +0.1/-0.5mm
T	11mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	360

Specifications

Capacitance	1.5 uF
Tolerance	20%
Voltage DC	520 VDC
Voltage AC	250 VAC
Temperature Range	-40/+110°C
Rated Temperature	105°C
Dissipation Factor	0.1% 25C
Insulation Resistance	20 GOhms
Max dV/dt	120 V/us
ESR	63.7 mOhms (100kHz)
Ripple Current	2.02 Amps (100kHz 85C), 180 Amps (Peak)
Inductance	18 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.