


R73RI1220DQ00K

Aliases (73RI1220DQ00K)

R73, Film, Film/Foil Polypropylene, Automotive Grade, 2,200 pF, 10%, 1,250 VDC, 85° C, 15 mm



General Information	
Series	R73
Dielectric	Film/Foil Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.

Click here for the 3D model.

Dimensions	
L	18mm +0.3/-0.5mm
Н	11mm +0.1/-0.5mm
Т	5mm +0.2/-0.5mm
S	15mm +0.6/-0.1mm
НО	18.5mm +/-0.5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Ammo, 360x340x59mm, Box
Packaging Quantity	800

Specifications	
Capacitance	2,200 pF
Tolerance	10%
Voltage DC	1250 VDC
Voltage AC	450 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	30,000 V/us
Inductance	10 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/02/2025 © 2006 - 2025 YAGEO