



Click [here](#) for the 3D model.

#### General Information

Series	R752
Dielectric	Metallized Polypropylene
Style	Radial
Features	Pulse, Capacitive Power Supply
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut
AEC-Q200	No

#### Dimensions

L	26.5mm +/-0.3mm
H	15mm +0.1mm
T	6mm +/-0.2mm
S	22.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	805

#### Specifications

Capacitance	0.33 uF
Tolerance	10%
Voltage DC	400 VDC, 240 VDC (105C)
Voltage AC	230 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	200 V/us
Inductance	18 nH