


## R75MF2680DQ30K

Aliases (75MF2680DQ30K)

R75, Film, Metallized Polypropylene, Automotive Grade, 0.068 uF, 10%, 400 VDC, 85°C, 10 mm



Click	here	for the	3D	model.
CIICK	nere	Tor the	30	mode

<b>6</b> 1.1.1.11	
Side View	Dielectric
<del>&lt; →</del>	Style
	Features
	RoHS
\	Termination
	Lead
<i>T</i> -	Qualifications
7 "	AEC-Q200
	Typical Compone
	Missellenses

Dimensions	
L	13mm +0.2/-0.5mm
Н	12mm +0.1/-0.5mm
Т	6mm +0.2/-0.5mm
S	10mm +/-0.4mm
НО	18.5mm +/-0.5mm
F	0.6mm +/-0.05mm

Packaging Specifications		
Packaging	Ammo, 360x340x59mm, Box	
Packaging Quantity	680	

General Information	
Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	1.433 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.

Specifications	
Capacitance	0.068 uF
Tolerance	10%
Voltage DC	400 VDC
Voltage AC	220 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.04% 1kHz, 0.06% 10kHz
Insulation Resistance	100 GOhms
Max dV/dt	1,300 V/us
ESR	23.4 mOhms (100kHz)
Ripple Current	3.66 Amps (100kHz 85C), 88 Amps (Peak)
Inductance	9 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/21/2025 © 2006 - 2025 YAGEO