



Click [here](#) for the 3D model.

Dimensions

| | |
|----|--------------------|
| L | 41.5mm +0.3/-0.7mm |
| H | 19mm +0.1/-0.7mm |
| T | 24mm +0.3/-0.7mm |
| S | 37.5mm +/-0.4mm |
| LL | 25mm +2/-1mm |
| F | 1mm +/-0.4mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Tray |
| Packaging Quantity | 108 |

General Information

| | |
|--------------------------|---|
| Series | R75 |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | Pulse |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Typical Component Weight | 20.9 g |
| Miscellaneous | Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C. |

Specifications

| | |
|-----------------------|--|
| Capacitance | 3.9 uF |
| Capacitance Tolerance | 5% |
| Voltage DC | 400 VDC |
| Voltage AC | 220 VAC |
| Temperature Range | -55/+105°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.06% 1kHz, 0.08% 10kHz |
| Insulation Resistance | 7.6923 GOhms |
| Max dV/dt | 70 V/us |
| ESR | 6.121 mOhms (100kHz) |
| Ripple Current | 11.95 Amps (100kHz 85C), 273 Amps (Peak) |
| Inductance | 20 nH |