


R75PN3680CK30J

Aliases (75PN3680CK30J)

R75, Film, Metallized Polypropylene, Automotive Grade, 0.68 uF, 5%, 630 VDC, 85° C, 22.5 mm



General Information	
Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.

Click here for the 3D model.

Dimensions	
L	26.5mm +0.3/-0.5mm
Н	22mm +0.1/-0.5mm
Т	13mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
НО	18.5mm +/-0.5mm
F	0.8mm +/-0.05mm
T S HO	13mm +0.2/-0.5mm 22.5mm +/-0.4mm 18.5mm +/-0.5mm

Packaging Specifications		
Packaging	T&R, Large	
Packaging Quantity	300	

Specifications	
Capacitance	0.68 uF
Tolerance	5%
Voltage DC	630 VDC
Voltage AC	250 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.05% 1kHz, 0.08% 10kHz
Insulation Resistance	44.1176 GOhms
Max dV/dt	400 V/us
ESR	9.4 mOhms (100kHz)
Ripple Current	8.25 Amps (100kHz 85C), 272 Amps (Peak)
Inductance	16 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/26/2025 © 2006 - 2025 YAGEO