


R75RN2470DQ30K

Aliases (75RN2470DQ30K)

R75, Film, Metallized Polypropylene, Automotive Grade, 0.047 uF, 10%, 1,250 VDC, 85°C, 22.5 mm



Click	horo	for	tha	3D	model

General Information	
Series	R75
Dielectric	Metallized Polypropylene
Style	Radial
Features	Automotive Grade, Pulse
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	3.4 g
Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.

5mm +0.3/-0.5mm
m +0.1/-0.5mm
m +0.2/-0.5mm
5mm +/-0.4mm
mm +/-0.5mm
mm +/-0.05mm

Packaging Specifications	
Packaging	Ammo, 360x340x59mm, Box
Packaging Quantity	380

Specifications	
Capacitance	0.047 uF
Tolerance	10%
Voltage DC	1250 VDC
Voltage AC	600 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.04% 1kHz, 0.06% 10kHz, 0.25% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	2,100 V/us
ESR	16.9 mOhms (100kHz)
Ripple Current	5.37 Amps (100kHz 85C), 99 Amps (Peak)
Inductance	16 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO