

R76MW4820SE30K

Aliases (76MW4820SE30K)

R76, Film, Double Metallized Polypropylene, General Purpose, 8.2 uF, 10%, 400 VDC, 85°C, 37.5 mm



General Information	
Series	R76
Dielectric	Double Metallized Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut
AEC-Q200	No
Typical Component Weight	62.9 g

Click here for the 3D model.

Dimensions	
L	41.5mm +0.3/-0.7mm
Н	45mm +0.1/-0.7mm
Т	30mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	4mm +2mm
F	1mm +/-0.05mm

Packaging Specifications		
Packaging	Tray	
Packaging Quantity	90	

Specifications	
Capacitance	8.2 uF
Tolerance	10%
Voltage DC	400 VDC
Voltage AC	250 VAC
Temperature Range	-55/+110°C
Rated Temperature	85°C
Dissipation Factor	0.04% 1kHz
Insulation Resistance	3.6585 GOhms
Max dV/dt	180 V/us
ESR	2.33 mOhms (100kHz)
Ripple Current	14.6 Amps (100kHz 85C), 1476 Amps (Peak)
Inductance	20 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/25/2025 © 2006 - 2025 YAGEO