


R76UN1180DQ00J

Aliases (76UN1180DQ00J)

R76, Film, Double Metallized Polypropylene, Automotive Grade, 1,800 pF, 5%, 2,000 VDC, 85°C, 22.5 mm



| General Information | |
|---------------------|------------------------------------|
| Series | R76 |
| Dielectric | Double Metallized Polypropylene |
| Style | Radial |
| Features | Automotive Grade, Pulse |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Qualifications | AEC-Q200 |
| AFC-0200 | Yes |

Click here for the 3D model.

| Dimensions | |
|------------|--------------------|
| L | 26.5mm +0.3/-0.5mm |
| Н | 15mm +0.1/-0.5mm |
| Т | 6mm +0.2/-0.5mm |
| S | 22.5mm +/-0.4mm |
| НО | 18.5mm +/-0.5mm |
| F | 0.8mm +/-0.05mm |
| | |

| Packaging Specifications | |
|--------------------------|-------------------------|
| Packaging | Ammo, 360x340x59mm, Box |
| Packaging Quantity | 464 |

| Specifications | |
|-----------------------|---|
| Capacitance | 1,800 pF |
| Tolerance | 5% |
| Voltage DC | 2000 VDC |
| Voltage AC | 700 VAC |
| Temperature Range | -55/+110°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz |
| Insulation Resistance | 100 GOhms |
| Max dV/dt | 4,500 V/us |
| ESR | 353.68 mOhms (100kHz) |
| Ripple Current | 0.8 Amps (100kHz 85C), 8 Amps (Peak) |
| Inductance | 16 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO