

## R79PC1220JH40J

Aliases (79PC1220JH40J)

**General Information** 

Series Dielectric

Not for New Design

R79, Film, Metallized Polypropylene, General Purpose, 2,200 pF, 5%, 630 VDC, 85°C, 5 mm

R79

Metallized Polypropylene




image Not	Style	Radial
	Features	Pulse
Available	RoHS	Yes
Click here for the 3D model.	Termination	Cut (Tinned Wire)
	Lead	Cut
	AEC-Q200	No
	Typical Component Weight	0.3 g
	Miscellaneous	Above 85C DC And AC Voltage Derating Is 1.25%/C.
	Notes	Series Replaced by R75.
Dimensions	Specifications	

Dimensions	
L	7.2mm +0.2/-0.5mm
Н	7.5mm +0.1/-0.5mm
Т	3.5mm +0.1/-0.5mm
S	5mm +/-0.4mm
LL	3.2mm +0.3/-0.2mm
F	0.5mm +/-0.05mm

Packaging Specifications		
Packaging	Bulk, Bag	
Packaging Quantity	2000	

Specifications	
Capacitance	2,200 pF
Tolerance	5%
Voltage DC	630 VDC
Voltage AC	220 VAC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.06% 1kHz, 0.1% 10kHz, 0.3% 100kHz
Insulation Resistance	100 GOhms
Max dV/dt	500 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/18/2025 © 2006 - 2025 YAGEO