



Click [here](#) for the 3D model.

| Dimensions | |
|------------|-----------------|
| L | 7.2mm +0.3mm |
| H | 11mm +0.1mm |
| T | 6mm +0.2mm |
| S | 5mm +/-0.4mm |
| LL | 17mm +1/-2mm |
| F | 0.5mm +/-0.05mm |

| Packaging Specifications | |
|--------------------------|------|
| Packaging | Bulk |
| Packaging Quantity | 1000 |

| General Information | |
|--------------------------|--|
| Series | RSB |
| Dielectric | Metallized Polyester Stacked |
| Style | Radial |
| Features | Automotive Grade, DC Multipurpose Applications |
| RoHS | Yes |
| Lead | Wire Leads |
| Qualifications | AEC-Q200 |
| AEC-Q200 | Yes |
| Typical Component Weight | 0.706 g |
| Miscellaneous | Above 85C DC And AC Voltage Derating Is 1.25%/C. |

| Specifications | |
|-----------------------|-----------------------|
| Capacitance | 1.5 uF |
| Capacitance Tolerance | 10% |
| Voltage DC | 63 VDC |
| Voltage AC | 40 VAC |
| Temperature Range | -55/+125°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.8% 1kHz, 1.2% 10kHz |
| Insulation Resistance | 666.7 MOhms |
| Max dV/dt | 250 V/us |
| Inductance | 7 nH |