



Click [here](#) for the 3D model.

Dimensions

| | |
|-----------|--------------|
| D | 50mm MAX |
| H | 28mm MAX |
| LL | 3mm +/-0.5mm |
| S | 44mm NOM |
| Wire Size | 2.3mm |

Packaging Specifications

| | |
|--------------------------|-------|
| Packaging | Tray |
| Packaging Quantity | 60 |
| Typical Component Weight | 101 g |

General Information

| | |
|---------------|---|
| Series | SC Three Phase |
| Style | Through-Hole |
| Features | High Impedance |
| RoHS | Yes |
| Notes | Lead Spacing (S/S1) Are For Reference Only. |
| Miscellaneous | Temperature Rise Maximum: 40 K. |
| Core | Mn-Zn Ferrite |

Specifications

| | |
|-------------------|--------------------|
| Voltage AC | 500 VAC |
| Voltage DC | 500 VDC |
| Inductance | 0.1015 mH (10 kHz) |
| Current | 26 A |
| Temperature Range | -25/+120°C |
| DC Resistance | 1.5 mOhms |