


SCF39XV-240-2R4A011JH

General Information

Aliases (UALCF390011JH0)
Common Mode Chokes - Power, KEMET, SC39XV, Through-Hole, Common Mode, 3,000 uH, -30/+50%



Series	SC39XV
Style	Through-Hole
Features	High Rated Voltage
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Nanocrystal

Click	horo	for t	ha 2	Dmo	႕시

Dimensions	
D	53mm MAX
Н	31mm +1/-0.6mm
LL	4.5mm +/-0.5mm
S	24.84mm +/-0.5mm
S1	37.52mm +/-0.5mm
Wire Size	2.4mm
BD	51mm +/-0.5mm
ВТ	50mm +/-0.5mm

Specifications		
Voltage AC	1000 VAC	
Voltage DC	1000 VDC	
Inductance	3 mH	
Inductance Tolerance	-30/+50%	
Rated Current	24 A	
Temperature Range	-40/+150°C	
DC Resistance	3.04 mOhms	

Packaging Specifications	
Packaging	Tray
Packaging Quantity	48
Typical Component Weight	139.2 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO