


SHO-101

Aliases (UDLSHO01010000, SHO101) Common Mode Chokes - Signal, KEMET, SHO, Through-Hole, Common Mode, 2,000 nH



General Information	
Series	SHO
Style	Through-Hole
RoHS	Yes

50 VDC 2 uH

Click here for the 3D model.

Dimensions	
L	11mm MAX
T	7.5mm MAX
Н	11mm MAX
LL	10mm +/-3mm

11mm MAX	Temperature Range	-25/+70°C
10mm +/-3mm	DC Resistance	15.5 mOhms (per Line MAX)
Bulk. Box		

Inductance

Specifications
Voltage DC

Packaging	Bulk, Box
Packaging Quantity	6000
Typical Component Weight	1.16 g

Packaging Specifications

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/12/2025 © 2006 - 2025 YAGEO