



General Information

Series	SS11V/H-CH
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Inductance Measurement Condition: 1kHz 1V KC530.

Dimensions

L	21mm +/-1mm
T	20.5mm +/-1mm
H	16mm +/-1mm
LL	3.5mm +/-1mm
S	18mm +/-0.5mm
S1	14mm +/-0.5mm
F	0.8mm NOM

Specifications

Voltage AC	250 VAC
Inductance	9.3 mH
Rated Current	1 A
Temperature Range	-25/+120°C
DC Resistance	0.44 Ohms

Packaging Specifications

Typical Component Weight	11.1 g
--------------------------	--------