


SC-26-S010JH

Aliases (UALSC26S010JH)

KEMET, SC Three Phase, AC Line Filters, Common Mode, 0.1015 mH



Click [here](#) for the 3D model.

Dimensions

D	50mm MAX
H	28mm MAX
LL	3mm +/-0.5mm
S	44mm NOM
Wire Size	2.3mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	60
Typical Component Weight	101 g

General Information

Series	SC Three Phase
Style	Through-Hole
Features	High Impedance
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	500 VAC
Voltage DC	500 VDC
Inductance	0.1015 mH (10 kHz)
Current	26 A
Temperature Range	-25/+120°C
DC Resistance	1.5 mOhms