



Click [here](#) for the 3D model.

#### General Information

Series	SSHB10HS
Style	Through-Hole
RoHS	Yes
Notes	Marking: R11 Lot No.
Miscellaneous	Temperature Rise Maximum: 50 K.
Core	Mn-Zn Ferrite

#### Dimensions

L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm NOM
Wire Size	0.35mm
F	0.7mm NOM

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	300
Typical Component Weight	10 g

#### Specifications

Voltage AC	250 VAC, 320 VAC (IEC60664-1)
Rated Current	1.1 A
Temperature Range	-40/+120°C
DC Resistance	0.35 Ohms (Per Line)
Inductance Common Mode	10 mH
Inductance Differential Mode	135 uH