



Click [here](#) for the 3D model.

#### General Information

Series	SCR
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 55 K.
Core	Mn-Zn Ferrite

#### Specifications

Voltage AC	250 VAC
Inductance	25 mH
Rated Current	2 A
Temperature Range	-40/+120°C
DC Resistance	200 mOhms

#### Dimensions

L	29mm MAX
T	23mm MAX
H	29mm MAX
LL	3.5mm +/-0.5mm
S	18mm NOM
S1	16mm NOM
Wire Size	0.55mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	240
Typical Component Weight	23 g