




Click [here](#) for the 3D model.

### Dimensions

|    |                      |
|----|----------------------|
| D  | 7.34mm +0.41/-0.38mm |
| L  | 17.42mm +/-0.79mm    |
| L2 | 20.88mm MAX          |
| LL | 38.1mm +/-6.35mm     |
| F  | 0.64mm +/-0.05mm     |

### Packaging Specifications

|                    |            |
|--------------------|------------|
| Packaging          | T&R, 305mm |
| Packaging Quantity | 500        |

### General Information

|                |                                                                                                                            |
|----------------|----------------------------------------------------------------------------------------------------------------------------|
| Series         | T266 CSS21                                                                                                                 |
| Dielectric     | MnO2 Tantalum                                                                                                              |
| Style          | Axial Hermetic                                                                                                             |
| Description    | Axial, Solid Tantalum, Hermetically Sealed, Military, CSS21 Style                                                          |
| RoHS           | No                                                                                                                         |
| Prop 65        | <b>WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">http://www.p65warnings.ca.gov</a> . |
| Termination    | Lead (SnPb)                                                                                                                |
| Lead           | Wire Leads                                                                                                                 |
| Qualifications | CSS21                                                                                                                      |
| AEC-Q200       | No                                                                                                                         |
| Construction   | Hermetic                                                                                                                   |

### Specifications

|                       |                   |
|-----------------------|-------------------|
| Capacitance           | 100 uF            |
| Capacitance Tolerance | 5%                |
| Voltage DC            | 10 VDC (85C)      |
| Temperature Range     | -55/+125°C        |
| Rated Temperature     | 85°C              |
| Dissipation Factor    | 8% 1kHz 25C       |
| Failure Rate          | B (0.1%/1000 Hrs) |
| ESR                   | 0.1 Ohms (100kHz) |
| Leakage Current       | 5 uA              |