

**General Information** 

Series Dielectric

Style




T340, Tantalum, MnO2 Tantalum, Commercial Grade, 2.7 uF, 20%, 35 VDC, 6 Ohms, 5 mm

T340

MnO2 Tantalum

Radial Molded



	H	0.1,.0	
F-\-\	LL U	Description	Radial, Solid Tantalum, Molded
		RoHS	No
		Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
		SCIP Number	a3b4e2e1-63ea-439e-a89a-7432 25502a7d
		Termination	Lead (SnPb)
		AEC-Q200	No
Click here for the 3D model.		Construction	Molded
		Miscellaneous	Includes Standoff Height of 0.38 +/- 0.13mm.
		Notes	Longest Lead Is Positive.
Dimensions		Specifications	
		- ·	

Dimensions	
W	7.2mm MAX
Н	8.3mm MAX
T	4mm MAX
S	5mm +/-0.5mm
LL	15mm +/-2mm
F	0.5mm +/-0.03mm

Packaging Specifications			
Packaging	Bulk, Bag		
Packaging Quantity	300		

Specifications			
Capacitance	2.7 uF		
Tolerance	20%		
Voltage DC	35 VDC (85C), 23 VDC (125C), 0.35 VDC (125C Reverse)		
Temperature Range	-55/+125°C		
Dissipation Factor	6%		
ESR	6 Ohms (100kHz)		
Leakage Current	1uA		

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO