




T355, Tantalum, MnO2 Tantalum, Commercial Grade, 5.6 uF, 10%, 25 VDC, Radial, Solid Tantalum, Conformal, Dipped, 3.18 mm



Click here for the 3D model.

T355
MnO2 Tantalum
Radial
Radial, Solid Tantalum, Conformal, Dipped
Low Leakage, Reverse Voltage
No
WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov / .
Oc1392c3-c7b9-4178-827c-fa26 617a3178
Lead (SnPb)
No
Conformal
Longest Lead Is Positive.

Dimensions	
D	5.5mm
W	6.35mm +/-0.64mm
Н	10.2mm
S	3.18mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.5mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	1000

Specifications	
Capacitance	5.6 uF
Tolerance	10%
Voltage DC	25 VDC (85C), 16 VDC (125C), 0.25 VDC (125C Reverse)
Temperature Range	-55/+125°C
Dissipation Factor	5%
Leakage Current	1.1 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO