



Click [here](#) for the 3D model.

General Information

| | |
|--------------|---|
| Series | T356 |
| Dielectric | MnO2 Tantalum |
| Style | Radial |
| Description | Radial, Solid Tantalum, Conformal, Dipped |
| Features | Low Leakage, Reverse Voltage |
| RoHS | Yes |
| Termination | Tin |
| AEC-Q200 | No |
| Construction | Conformal |
| Notes | Longest Lead Is Positive. |

Specifications

| | |
|--------------------|--|
| Capacitance | 4.7 uF |
| Tolerance | 20% |
| Voltage DC | 35 VDC (85C), 23 VDC (125C), 0.35 VDC (125C Reverse) |
| Temperature Range | -55/+125°C |
| Dissipation Factor | 5% |
| Leakage Current | 1.3 uA |

Dimensions

| | |
|---|------------------|
| D | 5.5mm |
| H | 10.2mm |
| S | 5.08mm +/-0.38mm |
| F | 0.5mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, 305mm |
| Packaging Quantity | 1000 |