



Click [here](#) for the 3D model.

General Information

| | |
|--------------|--|
| Series | T368 |
| Dielectric | MnO2 Tantalum |
| Style | Radial |
| Description | Radial, Solid Tantalum, Conformal, Rectangular Anode |
| Features | Rectangular Anode |
| RoHS | Yes |
| Termination | Tin |
| AEC-Q200 | No |
| Construction | Conformal |
| Notes | Longest Lead Is Positive. |

Specifications

| | |
|--------------------|--------------------------------------|
| Capacitance | 10 uF |
| Tolerance | 10% |
| Voltage DC | 35 VDC (85C), 1.75 VDC (85C Reverse) |
| Temperature Range | -55/+85°C |
| Dissipation Factor | 6% |
| Leakage Current | 2.8 uA |

Dimensions

| | |
|----|------------------|
| W | 10.16mm |
| H | 10.67mm +2.54mm |
| T | 6.35mm |
| S | 6.35mm +/-0.38mm |
| LL | 4.75mm +/-0.81mm |
| F | 0.64mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 500 |