




T368, Tantalum, MnO2 Tantalum, Commercial Grade, 6.8 uF, 20%, 50 VDC, Radial, Solid Tantalum, Conformal, Retangular Anode, 6.35 mm



Click here for the 3D model.

General Information	
Series	T368
Dielectric	MnO2 Tantalum
Style	Radial
Description	Radial, Solid Tantalum, Conformal, Retangular Anode
Features	Rectangular Anode
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	Oc1392c3-c7b9-4178-827c-fa2 6617a3178
Termination	Lead (SnPb)
AEC-Q200	No
Construction	Conformal
Notes	Longest Lead Is Positive.

).16mm
).67mm +2.54mm
.35mm
.35mm +/-0.38mm
Bmm MIN
.64mm +/-0.05mm
3

Packaging Specifications	
Packaging	T&R, 305mm
Packaging Quantity	500

6.8 uF
20%
50 VDC (85C), 2.5 VDC (85C Reverse)
-55/+85°C
5%
2.7 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/30/2025 © 2006 - 2025 YAGEO