


## T396K106M050AS

T396, Tantalum, MnO2 Tantalum, Commercial Grade, 10 uF, 20%, 50 VDC, Radial, Solid Tantalum, Three Leaded, 2.54 mm





Click here for the 3D model.

General Information	
Series	T396
Dielectric	MnO2 Tantalum
Style	Radial Three Lead
Description	Radial, Solid Tantalum, Three Leaded
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	78c25989-fc86-4b0d-a598-1bc ecbae95c0
Termination	Lead (SnPb)
AEC-Q200	No
Construction	Conformal
Notes	Longest Lead Is Positive.

Dimensions	
W	8.6mm
Н	12.7mm
Т	8.6mm
S	2.54mm +/-0.2mm
LL	4.75mm +/-1.27mm
F	0.5mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	250

10 uF
20%
50 VDC (85C), 33 VDC (125C), 0.5 VDC (125C Reverse)
-55/+125°C
6%
4 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO