


T493C685K035BT6120

T493 HRA, Tantalum, MnO2 Tantalum, HRA, 6.8 uF, 10%, 35 VDC, SMD, MnO2, Molded, High Reliability, B (0.1%/1000 Hrs), 900 mOhms, 6032, 2.8 mm, 1.3 mm



| General Information | |
|--------------------------|--|
| Series | T493 HRA |
| Dielectric | MnO2 Tantalum |
| Style | SMD Chip |
| Description | SMD, MnO2, Molded, High Reliability |
| Features | High Reliability |
| RoHS | Yes |
| Termination | Tin |
| AEC-Q200 | No |
| Typical Component Weight | 224.2 mg |
| Notes | P and R dimensions represents the minimum solderable area of the termination surface entirely below cutout (if one is present). |
| | |

| Dimensions | |
|------------|--------------------|
| L | 6mm +/-0.3mm |
| W | 3.2mm +/-0.3mm |
| Н | 2.5mm +/-0.3mm |
| Т | 0.13mm REF |
| S | 1.3mm +/-0.3mm |
| F | 2.2mm +/-0.1mm |
| A | 3.1mm MIN |
| В | 0.5mm +/-0.15mm |
| Е | 2.4mm REF |
| G | 2.8mm REF |
| P | 0.5mm MIN |
| R | 1mm REF |
| X | 0.1mm +/-0.1mm REF |

| Specifications | |
|-------------------------|-----------------------------------|
| эреспісацопа | |
| Capacitance | 6.8 uF |
| Tolerance | 10% |
| Voltage DC | 35 VDC (85C), 23.45 VDC (125C) |
| Temperature Range | -55/+125°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 6% 120Hz 25C |
| Failure Rate | B (0.1%/1000 Hrs) |
| ESR | 0.9 Ohms (100kHz 25C) |
| Ripple Current | 350 mA (rms, 100kHz 25C) |
| Leakage Current | 2.4 uA (5min 25°C) |
| Testing and Reliability | Standard Testing Only |

| Packaging Specifications | |
|--------------------------|------------|
| Packaging | T&R, 178mm |
| Packaging Quantity | 500 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO