


T493D336M035CH641A

T493 Space, Tantalum, MnO2 Tantalum, Space, 33 uF, 20%, 35 VDC, SMD, MnO2, Molded, Aerospace, C (0.01%/1000 Hrs), 300 mOhms, 7343, 3.1 mm, 1.3 mm



General Information	
Series	T493 Space
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, MnO2, Molded, Aerospace
Features	Aerospace
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	1dd2e1b8-26dd-4d52-927c-6f9 d519011aa
Termination	Tin Lead (SnPb)
AEC-Q200	No
Typical Component Weight	412.33 mg
Notes	P and R dimensions represents the minimum solderable area of the termination surface entirely below cutout (if one is present).

3mm +/-0.3mm
3mm +/-0.3mm
8mm +/-0.3mm
13mm REF
3mm +/-0.3mm
4mm +/-0.1mm
8mm MIN
5mm +/-0.15mm
5mm REF
5mm REF
nm MIN
5mm MIN
nm REF
1mm +/-0.1mm REF

Specifications	
Capacitance	33 uF
Tolerance	20%
Voltage DC	35 VDC (85C), 23.45 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6% 120Hz 25C
Failure Rate	C (0.01%/1000 Hrs)
ESR	0.3 Ohms (100kHz 25C)
Ripple Current	707 mA (rms, 100kHz 25C)
Leakage Current	11.6 uA (5min 25°C)
Testing and Reliability	10 Cycles Surge Testing At -55C And +85C Before Weibull; Additional Testing Option A

Packaging Specifications	
Packaging	T&R, 178mm
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/16/2025 © 2006 - 2025 YAGEO