


## T495B685M016ATE1K2

T495, Tantalum, MnO2 Tantalum, Commercial Grade, 6.8 uF, 20%, 16 VDC, SMD, MnO2, Molded, Low ESR, 1.2 Ohms, 3528, 2.1 mm, 0.8 mm





Click	here	for	the	3D	model.
-------	------	-----	-----	----	--------

General Information		
Series	T495	
Dielectric	MnO2 Tantalum	
Style	SMD Chip	
Description	SMD, MnO2, Molded, Low ESR	
Features	Low ESR	
RoHS	Yes	
Termination	Tin	
AEC-Q200	No	
Typical Component Weight	107.45 mg	
Shelf Life	156 Weeks	
MSL	1	

Dimensions	
L	3.5mm +/-0.2mm
W	2.8mm +/-0.2mm
Н	1.9mm +/-0.2mm
Т	0.13mm REF
S	0.8mm +0.1/-0.3mm
F	2.2mm +/-0.1mm
A	1.9mm MIN
В	0.4mm +/-0.15mm
E	2.2mm REF
G	1.8mm REF
P	0.5mm REF
R	1mm REF
X	0.1mm +/-0.1mm REF

Packaging Specifications		
Packaging	T&R, 178mm	
Packaging Quantity	2000	

Specifications	
Capacitance	6.8 uF
Tolerance	20%
Voltage DC	16 VDC (85C), 10.72 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6% 120Hz 25C
Failure Rate	N/A
ESR	1200 mOhms (100kHz 25C)
Ripple Current	266 mA (rms, 100kHz 25C), 239.4 mA (rms, 85C), 106.4 mA (rms, 125C)
Leakage Current	1.1 uA (5min 25°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/17/2025 © 2006 - 2025 YAGEO