

T497H475K050CH642B

T497 Space, Tantalum, MnO2 Tantalum, Space, 4.7 uF, 10%, 50 VDC, SMD, MnO2, Molded, Aerospace, Medical, C (0.01%/1000 Hrs), 500 mOhms, 7238, 3.17 mm, 1.27 mm



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|---|
| Series | T497 Space |
| Dielectric | MnO2 Tantalum |
| Style | SMD Chip |
| Description | SMD, MnO2, Molded, Aerospace, Medical |
| Features | Aerospace, Medical |
| RoHS | No |
| Prop 65 | WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/ |
| SCIP Number | 1dd2e1b8-26dd-4d52-927c-6f9d519011aa |
| Termination | Tin Lead (SnPb) |
| AEC-Q200 | No |
| Typical Component Weight | 349.01 mg |
| Notes | Note: When solder coated terminations are required, add an additional 0.38mm (0.015inch) to the tolerances for "L", "W", "H", "K", "F" and "S". |

Dimensions

| | |
|---|----------------------|
| L | 7.24mm +/-0.38mm |
| W | 3.81mm +/-0.38mm |
| H | 2.79mm +/-0.38mm |
| S | 1.27mm +0.25/-0.13mm |
| F | 3.68mm +0.13/-0.51mm |
| K | 1.52mm MIN |
| P | 0.76mm MIN |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, 178mm |
| Packaging Quantity | 500 |

Specifications

| | |
|-------------------------|--|
| Capacitance | 4.7 uF |
| Tolerance | 10% |
| Voltage DC | 50 VDC (85C), 33.5 VDC (125C) |
| Temperature Range | -55/+125°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 6% 120Hz 25C |
| Failure Rate | C (0.01%/1000 Hrs) |
| ESR | 0.5 Ohms (100kHz 25C) |
| Ripple Current | 548 mA (rms, 100kHz 25C) |
| Leakage Current | 3 uA (5min 25°C) |
| Testing and Reliability | 10 Cycles Surge Testing At -55C And +85C Before Weibull; Additional Testing Option B |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.