


T497X156K035CH642B

T497 Space, Tantalum, MnO2 Tantalum, Space, 15 uF, 10%, 35 VDC, SMD, MnO2, Molded, Aerospace, Medical, C (0.01%/1000 Hrs), 190 mOhms, 6954, 3.12 mm, 1.19 mm



T497 Space
MnO2 Tantalum
SMD Chip
SMD, MnO2, Molded, Aerospace, Medical
Aerospace, Medical
No
WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
1dd2e1b8-26dd-4d52-927c-6f9 d519011aa
Tin Lead (SnPb)
No
590.44 mg
Note: When solder coated terminations are required, add an additional 0.38mm (0.015inch) to the tolerances for "L", "W", "H", "K", "F" and "S".

Dimensions	
L	6.93mm +/-0.38mm
W	5.41mm +/-0.38mm
Н	2.74mm +/-0.38mm
S	1.19mm +0.25/-0.13mm
F	3.05mm +/-0.13mm
K	1.22mm MIN
P	0.61mm MIN
Packaging Specifications	
Packaging	T&R, 178mm

500

Packaging Quantity

Specifications	
Capacitance	15 uF
Tolerance	10%
Voltage DC	35 VDC (85C), 23.45 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6% 120Hz 25C
Failure Rate	C (0.01%/1000 Hrs)
ESR	0.19 Ohms (100kHz 25C)
Ripple Current	932 mA (rms, 100kHz 25C)
Leakage Current	6 uA (5min 25°C)
Testing and Reliability	10 Cycles Surge Testing At -55C And +85C Before Weibull; Additional Testing Option B

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/21/2025 © 2006 - 2025 YAGEO