


T495, Tantalum, MnO2 Tantalum, Commercial Grade, 68 uF, 20%, 10 VDC, SMD, MnO2, Molded, Low Profile, Low ESR, 140 mOhms, 2 mm, 1.3 mm, 2817 / 7343



Click here f	for the	3D m	nodel.
--------------	---------	------	--------

Dimensions	
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
Н	1.8mm +/-0.2mm
Т	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.6mm MIN
E	3.5mm REF
G	3.5mm REF
X	0.05mm REF

Packaging Specifications	
Packaging	T&R, 178mm
Packaging Quantity	1000

General Information	
Series	T495
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, MnO2, Molded, Low Profile, Low ESR
Features	Low ESR
RoHS	Yes
Termination	Tin
AEC-Q200	No
Typical Component Weight	286.4 mg
Shelf Life	156 Weeks
MSL	1

Specifications	
Capacitance	68 uF
Tolerance	20%
Voltage DC	10 VDC (85C), 6.7 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6% 120Hz 25C
Failure Rate	N/A
ESR	140 mOhms (100kHz 25C)
Ripple Current	945 mA (rms, 100kHz 25C), 850.5 mA (rms, 85C), 378 mA (rms, 125C)
Leakage Current	6.8 uA (5min 25°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.


Generated 12/08/2025 © 2006 - 2025 YAGEO





T495, Tantalum, MnO2 Tantalum, Commercial Grade, 68 uF, 20%, 10 VDC, SMD, MnO2, Molded, Low Profile, Low ESR, 140 mOhms, 2 mm, 1.3 mm,  $2817\,/\,7343$ 


#### **Simulations**


For the complete simulation environment please visit Y-SIM.
















Generated 12/08/2025 © 2006 - 2025 YAGEO



T495, Tantalum, MnO2 Tantalum, Commercial Grade, 68 uF, 20%, 10 VDC, SMD, MnO2, Molded, Low Profile, Low ESR, 140 mOhms, 2 mm, 1.3 mm, 2817 / 7343





Generated 12/08/2025 © 2006 - 2025 YAGEO



T495, Tantalum, MnO2 Tantalum, Commercial Grade, 68 uF, 20%, 10 VDC, SMD, MnO2, Molded, Low Profile, Low ESR, 140 mOhms, 2 mm, 1.3 mm, 2817 / 7343

#### These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR used for ripple Ripple Currenty voltage vs. Frequency plots is the ESR at ambient temperature.
  The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated.
  The effects shown herein are based on measured data from a multiple part sample of the parts in question.
  Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.
  The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

   Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 12/08/2025 © 2006 - 2025 YAGEO