


**Obsolete**

B45197A, Tantalum, MnO<sub>2</sub> Tantalum, Commercial Grade, 47 uF, 10%, 35 VDC, SMD, Molded, Low ESR, Surge Robust, 230 mOhms, 4.4 mm, 1.3 mm, 2817 / 7343



**Dimensions**

L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	4.1mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm

**Packaging Specifications**

Packaging	T&R, 330mm
Packaging Quantity	1800

**General Information**

Series	B45197A
Dielectric	MnO <sub>2</sub> Tantalum
Style	SMD Chip
Description	SMD, Molded, Low ESR, Surge Robust
Features	Low ESR, Surge Robust
RoHS	Yes
Termination	Tin
AEC-Q200	No

**Specifications**

Capacitance	47 uF
Tolerance	10%
Voltage DC	35 VDC (85C), 23.45 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	6%
Failure Rate	N/A
ESR	0.23 Ohms (100kHz)
Ripple Current	850 mAmps (25C), 765 mAmps (85C), 340 mAmps (125C)
Leakage Current	16 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.