

T498D226K016ATE800

T498, Tantalum, MnO₂ Tantalum, High Temperature, 22 uF, 10%, 16 VDC, SMD, MnO₂, Molded, Hi-Temp, 150C, Auto, AEC-Q200, N/A, 800 mOhms, 7343, 3.1 mm, 1.3 mm



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|---|
| Series | T498 |
| Dielectric | MnO ₂ Tantalum |
| Style | SMD Chip |
| Description | SMD, MnO ₂ , Molded, Hi-Temp, 150C, Auto, AEC-Q200 |
| Features | Automotive, 150C |
| RoHS | Yes |
| Termination | Tin |
| Qualifications | AEC-Q200 |
| AEC-Q200 | Yes |
| Typical Component Weight | 446.84 mg |
| Shelf Life | 156 Weeks |
| MSL | 1 |

Dimensions

| | |
|---|--------------------|
| L | 7.3mm +/-0.3mm |
| W | 4.3mm +/-0.3mm |
| H | 2.8mm +/-0.3mm |
| T | 0.13mm REF |
| S | 1.3mm +/-0.3mm |
| F | 2.4mm +/-0.1mm |
| A | 3.8mm MIN |
| B | 0.5mm +/-0.15mm |
| E | 3.5mm REF |
| G | 3.5mm REF |
| P | 0.9mm REF |
| R | 1mm REF |
| X | 0.1mm +/-0.1mm REF |

Specifications

| | |
|--------------------|---|
| Capacitance | 22 uF |
| Tolerance | 10% |
| Voltage DC | 16 VDC (85C), 12.75 VDC (125C), 10.72 VDC (150C) |
| Temperature Range | -55/+150°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 4.5% 120Hz 25C |
| Failure Rate | N/A |
| ESR | 800 mOhms (100kHz 25C) |
| Ripple Current | 433 mA (rms, 100kHz 25C), 389.7 mA (rms, 85C), 129.9 mA (rms, 150C) |
| Leakage Current | 3.5 uA (5min 25°C) |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | T&R, 178mm |
| Packaging Quantity | 500 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.