


T520, Tantalum, Polymer Tantalum, Commercial Grade, 330 uF, 20%, 3 VDC, SMD, Polymer, Molded, Low Profile/ESR, NonCombustible, 15 mOhms, 1.9 mm, 1.3 mm, 2817 / 7343



Click	here	for	the	3D	model.
-------	------	-----	-----	----	--------

Dimensions

Packaging Quantity

L	7.3mm +/-0.3mm			
W	4.3mm +/-0.3mm			
Н	1.8mm +/-0.1mm			
Т	0.13mm REF			
S	1.3mm +/-0.3mm			
F	2.4mm +/-0.1mm			
A	3.8mm MIN			
X	0.05mm REF			
Packaging Specifications				
Packaging	T&R, 178mm			

1000

General Information			
Series	T520		
Dielectric	Polymer Tantalum		
Style	SMD Chip		
Description	SMD, Polymer, Molded, Low Profile/ESR, NonCombustible		
Features	Low ESR		
RoHS	Yes		
Termination	Tin		
AEC-Q200	No		
Typical Component Weight	274.3 mg		
Shelf Life	52 Weeks		
MSL	3		

Specifications		
Capacitance	330 uF	
Tolerance	20%	
Voltage DC	3 VDC (105C)	
Temperature Range	-55/+105°C	
Rated Temperature	105°C	
Life	2000 Hrs (105C)	
Humidity	60C, 90% RH, 500 Hours, No Load	
Dissipation Factor	10% 120Hz 25C	
Failure Rate	N/A	
ESR	15 mOhms (100kHz 25C)	
Ripple Current	3500 mA (rms, 100kHz 45C), 2450 mA (rms, 85C), 875 mA (rms, 105C)	
Leakage Current	99 uA (5min 25°C)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.


Generated 12/06/2025 © 2006 - 2025 YAGEO





T520, Tantalum, Polymer Tantalum, Commercial Grade, 330 uF, 20%, 3 VDC, SMD, Polymer, Molded, Low Profile/ESR, NonCombustible, 15 mOhms, 1.9 mm, 1.3 mm, 2817 / 7343


### **Simulations**


For the complete simulation environment please visit Y-SIM.
















Generated 12/06/2025 © 2006 - 2025 YAGEO



T520, Tantalum, Polymer Tantalum, Commercial Grade, 330 uF, 20%, 3 VDC, SMD, Polymer, Molded, Low Profile/ESR, NonCombustible, 15 mOhms, 1.9 mm, 1.3 mm, 2817 / 7343





Generated 12/06/2025 © 2006 - 2025 YAGEO



T520, Tantalum, Polymer Tantalum, Commercial Grade, 330 uF, 20%, 3 VDC, SMD, Polymer, Molded, Low Profile/ESR, NonCombustible, 15 mOhms, 1.9 mm, 1.3 mm, 2817 / 7343

### These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR in the "Temperature Rise vs. Ripple Current" plots is the ESR at ambient temperature. The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated. The effects shown herein are based on measured data from a multiple part sample of the parts in question. Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

  The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

  Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 12/06/2025 © 2006 - 2025 YAGEO