


## T556B107K010AT

T556, Tantalum, Polymer Tantalum, HRA, 100 uF, 10%, 10 VDC, N/A, 140 mOhms, 9.6 mm, 3 mm





General Information	
Series	T556
Dielectric	Polymer Tantalum
Style	SMD Chip
RoHS	No
SCIP Number	43449f08-bd3e-4b72-a04c-6c a7dd4144ff
Termination	Tin
AEC-Q200	No
Typical Component Weight	5.54 g
Shelf Life	156 Weeks

Click here for the 3D model.

Dimensions	
L	24.5mm +/-0.5mm
W	8.5mm +/-0.5mm
Н	9.1mm +/-0.5mm
S	3mm MIN
F	4.2mm +/-0.5mm
Packaging Specifications	

Bulk, Box 100

Packaging

Packaging Quantity

Specifications	
Capacitance	100 uF
Tolerance	10%
Voltage DC	10 VDC, 7.8 VDC (105°C), 6.6 VDC (125°C)
Temperature Range	-55/+125°C
Life	2000 Hrs
Dissipation Factor	5% (120Hz 25C)
Failure Rate	N/A
ESR	140 mOhm (100kHz 25C)
Ripple Current	1400 mAmps (40kHz 85C)
Leakage Current	7.5 uA (5min 25°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and
we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the
requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us
with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO