


## TRS5-100BSR01EV

Aliases (USEF100BSR01E0)

KEMET, TRS, Thermal Reed Switch, Radial, 2.5C Temperature Accuracy, High Reliability, High-Speed Response, Long Operational Life, Excellent Environmental Durability, High Temperature Accuracy, 100°C, Break



General Information	
Series	TRS
Туре	Thermal Reed Switch
Style	Radial
Description	Thermal Reed Switch
Features	High Reliability, High-Speed Response, Long Operational Life, Excellent Environmental Durability, High Temperature Accuracy
Lead	Cables
RoHS	Yes
REACH	Yes

Click here for the 3D model.

Dimensions	
D	8.1mm NOM
L	43mm NOM
LL	200mm NOM

Packaging Specifications		
Packaging	Rubberband Box	
Packaging Quantity	500	
Typical Component Weight	6.6 q	

Specifications	
Switching Temp.	100C +/-2.5C
Temperature Range	-20/+100°C
Contact Type	Break
Voltage DC	200 VDC MAX (Opening/ Closing)
Current	0.275 Amps AC MAX (Opening/ Closing), 1 mAmps MIN (5VDC, Opening/Closing)
ESR	300 mOhms MAX (Contact Resistance)
Max Opening/Closing Power	60.5 (AC/DC)
Max Opening/Closing Voltage	264 (AC)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/04/2025 © 2006 - 2025 YAGEO