



SIDE VIEW



ANODE (+) END VIEW



Click [here](#) for the 3D model.

General Information

Series	TSM
Dielectric	MnO2 Tantalum
Style	Stacked Chip
Description	SMD, MnO2, Stacks, High Reliability
Features	High Reliability
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
SCIP Number	30e82d35-b509-48ec-8c77-2d5ec01b3abc
Termination	Tin Lead (SnPb)
AEC-Q200	No
MSL	1

Dimensions

Case Code	3D
L	8mm +/-0.38mm
W	4.4mm +/-0.2mm
H	9.2mm +/-0.38mm
S	1.9mm +/-0.38mm
F	3mm +/-0.2mm
K	7.7mm +/-0.38mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	50

Specifications

Capacitance	660 uF
Tolerance	20%
Voltage DC	10 VDC (85C), 6.7 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	8% 120Hz 25C
Failure Rate	N/A
ESR	0.167 Ohms (100kHz 25C)
Leakage Current	66 uA (5min 25°C)
Testing and Reliability	10 Cycles Surge Current Testing At -55C And +85C Before Weibull

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.