




TRR Indust X7R HT260C, Ceramic, 3.3 uF, 10%, 50 VDC, X7R, Commercial, High Temperature, 10.16 mm



Click here for the 3D n	nodel
-------------------------	-------

General Information	
Series	TRR Indust X7R HT260C
Style	Radial
Description	Commercial, High Temperature
Features	High Temperature
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	a5a9e204-6d6a-49c3-acf7-37 d0b4e9df91
Termination	Gold
Lead	Wire Leads
AEC-Q200	No

Dimensions	
L	12.7mm MAX
W	12.7mm MAX
Т	3.81mm MAX
S	10.16mm
LL	31.75mm MIN
F	0.635mm +/-0.051mm

Packaging Specifications	
Packaging	Waffle, Tray
Packaging Quantity	20

Specifications	
Capacitance	3.3 uF
Tolerance	10%
Voltage DC	50 VDC
Dielectric Withstanding Voltage	125 VDC
Temperature Range	-55/+260°C
Temp. Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	15%, 1kHz 1.0Vrms
Dissipation Factor	2.5%1kHz1.0Vrms
Aging Rate	2% Loss/Decade Hour
Insulation Resistance	303.0303 MOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/24/2025 © 2006 - 2025 YAGEO