
UD2-3SNU-L

KEMET, UD2, Relays, Signal





gle

Click here for the 3D model.

Dimensions	
Н	5.45mm MAX
L	10.6mm +/-0.3mm
W	6.5mm +/-0.3mm
LL	0.25mm NOM
S	5.08mm +/-0.15mm
S1	2.2mm +/-0.15mm
F	0.8mm +/-0.1mm
F1	1.86mm +/-0.1mm

Packaging Specifications		
Packaging	T&R	

-40/+85°C
3 V
2 Form C (DPDT)
1A
90 Ohms +/-10%
Silver alloy with gold alloy overlay
2.25 (Set/Reset)
100 mW
30 W, 37.5 VA
220 V
250 VAC
>10A
1Amps
100 mOhms
Approximately 2ms
Approximately 1ms
1GOhms
1000 VAC (1min) 1500 V Surge

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/23/2025 © 2006 - 2025 YAGEO